



Arioso Recessed LED

2x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens

2x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens - 94 lm/W

The Day-Brite / CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

Product data

General information		Efficacy	
Lamp Source Code	LED	94 lm/W	
Colour Temperature	3500 K	Product data	
CRI	80	Order product name	2AVEG38L835-4-ACR-UNV-DIM
Photometric Distribution Type	Direct	EAN/UPC - Product	782343164310
Mounting	Recessed T-Bar / T-Grid	Order code	2AVEG38L835-4-ACR-UNV
Operating and electrical		Numerator - Quantity Per Pack	1
Voltages	UNIV V	Numerator - Packs per outer box	1
Luminaire Input Watts	40.5	Material Nr. (12NC)	912400392284
Mechanical and housing		Net Weight (Piece)	10.000 kg
Fixture Size	2 ft x 4 ft	Catalog Number	2AVEG38L835-4-ACR-UNV
Shape	Rectangular	Catalog Number Description	2x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens
Initial performance (IEC compliant)			
Luminaire Lumens	3800		