



DuaLED Surface LED

2x4, 7300 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount

2x4, 7300 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount - 99 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

Product data

General Information		Luminaire Input Watts	
Lamp Source Code	LED	74	
Colour Temperature	3500K	Mechanical and Housing	
CRI	80	Fixture Size	2 ft x 4 ft
Photometric Distribution Type	Direct	Shape	Rectangular
Mounting	Surface	Initial Performance (IEC Compliant)	
Operating and Electrical		Luminaire Lumens	7300
Voltages	120/277/347 V	Efficacy	99 lm/W

DuaLED Surface LED

Product Data

Order product name	2SDL73L835-4-D-UNV
EAN/UPC - Product	782343313183
Order code	2SDL73L835-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400393087

Net Weight (Piece)	0.001 kg
Catalog Number	2SDL73L835-4-D-UNV-DIM
Catalog Number Description	2x4, 7300 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount

