



LSW

LS2R114UNV

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep,

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

General Information	
Lamp Envelope Code	T-5
Lamp Watts	14
Number of Lamps	1
Mounting	Wall Surface
Operating and Electrical	
Voltages	277 V
Mechanical and Housing	
Fixture Size	24 in
Product Data	
Order product name	LS2R114UNV

EAN/UPC - Product	782343487051
Order code	912400394220
Local order code	4348705
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400394220
Net Weight (Piece)	0.001 kg
Commercial Code	LS2R114UNVPG
Catalog Number Description	Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep,