



LSW

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 28 watt T5 48" length luminaire

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 28 watt T5 48" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

General Information		EAN/UPC - Product	
Lamp Envelope Code	T-5	EAN/UPC - Product	782343487044
Lamp Watts	28	Order code	LS4R128UNVPG
Number of Lamps	1	Numerator - Quantity Per Pack	1
Mounting	Wall Surface	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400394221
Voltages	277 V	Net Weight (Piece)	0.001 kg
Mechanical and Housing		Catalog Number	LS4R128UNVPG
Fixture Size	48 in	Catalog Number Description	Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 28 watt T5 48" length luminaire
Product Data			
Order product name	LS4R128UNV		