



# DuaLED Recessed

**2x2, 3800 Nominal Delivered Lumens, 4000K, Diffuse**

2x2, 3800 Nominal Delivered Lumens, 4000K, Diffuse – 97 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

## Product data

General Information		Mechanical and Housing	
Lamp Source Code	LED	Fixture Size	2 ft x 2 ft
Colour Temperature	4000K	Shape	Square
CRI	80	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Direct	Luminaire Lumens	3800
Mounting	Recessed	Efficacy	97 lm/W
Operating and Electrical		Product Data	
Voltages	120/277/347 V	Order product name	2DLG38L840-2-D-UNV
Luminaire Input Watts	39	EAN/UPC – Product	782343781098
		Order code	2DLG38L840-2-D-UNV-DIM

## DuaLED Recessed

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400395153
Net Weight (Piece)	0.001 kg

Catalog Number	2DLG38L840-2-D-UNV-DIM
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 4000K, Diffuse

