



# LSW

## LS2R214UNV

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 14 watt T5 24" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

### Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>	782343513293
Lamp Envelope Code	T-5	Order code	912400396624
Lamp Watts	14	Local order code	4351329
Number of Lamps	2	Numerator - Quantity Per Pack	1
Mounting	Wall Surface	Numerator - Packs per outer box	1
<b>Operating and Electrical</b>		Material Nr. (12NC)	912400396624
Voltages	277 V	Net Weight (Piece)	0.001 kg
<b>Mechanical and Housing</b>		Commercial Code	LS2R214UNVPG
Fixture Size	24 in	Catalog Number Description	Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 14 watt T5 24" length luminaire
<b>Product Data</b>			
Order product name	LS2R214UNV		