



## LSW

### Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 17 watt T8 24" length luminaire

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 17 watt T8 24" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

#### Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>	782343488294
Lamp Envelope Code	T-8	<b>Order code</b>	LS2R217UNVHI
Lamp Watts	17	<b>Numerator - Quantity Per Pack</b>	1
Number of Lamps	2	<b>Numerator - Packs per outer box</b>	1
Mounting	Wall Surface	<b>Material Nr. (12NC)</b>	912400396766
<b>Operating and Electrical</b>		<b>Net Weight (Piece)</b>	0.001 kg
Voltages	277 V	<b>Catalog Number</b>	LS2R217UNVHI
<b>Mechanical and Housing</b>		<b>Catalog Number Description</b>	Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 17 watt T8 24" length luminaire
Fixture Size	24 in		
<b>Product Data</b>			
Order product name	LS2R217UNV		