



# LSW

## LS4R232UNV

TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 32 watt T8 48" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

### Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>	782343491287
Lamp Envelope Code	T-8	Order code	912400396929
Lamp Watts	32	Local order code	4349128
Number of Lamps	2	Numerator - Quantity Per Pack	1
Mounting	Wall Surface	Numerator - Packs per outer box	1
<b>Operating and Electrical</b>		Material Nr. (12NC)	912400396929
Voltages	277 V	Net Weight (Piece)	0.001 kg
<b>Mechanical and Housing</b>		Commercial Code	LS4R232UNVP2
Fixture Size	48 in	Catalog Number Description	TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 32 watt T8 48" length luminaire
<b>Product Data</b>			
Order product name	LS4R232UNV		