



LSW

TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 32 watt T8 48" length luminaire

TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 32 watt T8 48" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

General Information		EAN/UPC - Product 782343491287	
Lamp Envelope Code	T-8	Order code	LS4R232UNVP2
Lamp Watts	32	Numerator - Quantity Per Pack	1
Number of Lamps	2	Numerator - Packs per outer box	1
Mounting	Wall Surface	Material Nr. (12NC)	912400396929
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	277 V	Catalog Number	LS4R232UNVP2
Mechanical and Housing		Catalog Number Description	TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 32 watt T8 48" length luminaire
Fixture Size	48 in		
Product Data			
Order product name	LS4R232UNV		