



# DuaLED Surface LED

## 2x2, 3800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

2x2, 3800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse - 97 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface

Operating and Electrical	
Voltages	120/277/347 V

Luminaire Input Watts	39
-----------------------	----

Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square

Initial Performance (IEC Compliant)	
Luminaire Lumens	3800
Efficacy	97 lm/W

## DuaLED Surface LED

### Product Data

Order product name	2SDL38L840-2-D-UNV
EAN/UPC - Product	734340925746
Order code	2SDL38L840-2-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400397641

Net Weight (Piece)	0.001 kg
Catalog Number	2SDL38L840-2-D-UNV-DIM
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

