



# Arioso Recessed LED

## 1x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens

1x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens - 94 lm/W

The Day-Brite / CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

### Product data

<b>General information</b>		<b>Efficacy</b>	
Lamp Source Code	LED	94 lm/W	
Colour Temperature	3500 K	<b>Product data</b>	
CRI	80	Order product name	1AVEG38L835-4-ACR-UNV-DIM
Photometric Distribution Type	Direct	EAN/UPC - Product	781370218041
Mounting	Recessed T-Bar / T-Grid	Order code	1AVEG38L835-4-ACR-UNV
<b>Operating and electrical</b>		Numerator - Quantity Per Pack	1
Voltages	UNIV V	Numerator - Packs per outer box	1
Luminaire Input Watts	40.5	Material Nr. (12NC)	912400398193
<b>Mechanical and housing</b>		Net Weight (Piece)	0.001 kg
Fixture Size	1 ft x 4 ft	Catalog Number	1AVEG38L835-4-ACR-UNV
Shape	Rectangular	Catalog Number Description	1x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens
<b>Initial performance (IEC compliant)</b>			
Luminaire Lumens	3800		