



DuaLED Surface LED

1x4, 4700 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

1x4, 4700 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse - 92 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

Product data

General Information		Luminaire Input Watts 51	
Lamp Source Code	LED		
Colour Temperature	4000K	Mechanical and Housing	
CRI	80	Fixture Size	1 ft x 4 ft
Photometric Distribution Type	Direct	Shape	Rectangular
Mounting	Surface		
Operating and Electrical		Initial Performance (IEC Compliant)	
Voltages	120/277/347 V	Luminaire Lumens	4700
		Efficacy	92 lm/W

DuaLED Surface LED

Product Data

Order product name	1SDL47L840-4-D-UNV
EAN/UPC - Product	734340883077
Order code	1SDL47L840-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400398909

Net Weight (Piece)	0.001 kg
Catalog Number	1SDL47L840-4-D-UNV-DIM
Catalog Number Description	1x4, 4700 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

