



# BL616 Micro Accent

Accent, Aluminum Bullyte w/ Stake, Bronze, 7W LED, Flood, 2700K, 12V

Accent, Aluminum Bullyte w/ Stake, Bronze, 7W LED, Flood, 2700K, 12V - 100 lm/W

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

## Product data

General information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	Wide Flood
Mounting	NPT/NPS
Number Of Pieces	1
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	7
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	600
Efficacy	100 lm/W
Product data	
Order product name	BULLYTE,MICRO,W/STAKE
EAN/UPC - Product	783352017307
Order code	BL616-HS7LED7FLW
Numerator - Quantity Per Pack	1
Local code description	BL616-HS7LED7FLW
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400443760
Net Weight (Piece)	0.001 kg
Catalog Number	BL616-HS7LED7FLW
Catalog Number Description	Accent, Aluminum Bullyte w/ Stake, Bronze, 7W LED, Flood, 2700K, 12V