



i15 Inground

Inground, 12W LED, Narrow Flood, 4000K, 120V

Inground, 12W LED, Narrow Flood, 4000K, 120V – 100 lm/W

The revolutionary i1.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench – the i1.5 reinforces HADCO's position as the leader in landscape lighting.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	17
Number of Lamps	1
Colour Temperature	4000 K
CRI	80
Photometric Distribution Type	Medium
Mounting	In Ground
Number Of Pieces	1
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	17
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	800
Efficacy	100 lm/W
Product data	
Order product name	I15 INGROUND, LED
Order code	I15NNFC
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400443999
Net Weight (Piece)	0.010 kg
Catalog Number	I15NNFC
Catalog Number Description	Inground, 12W LED, Narrow Flood, 4000K, 120V