



BL616 Micro Accent

Accent, Aluminum w/ Stake, Bronze, 7W LED, Narrow Flood

Accent, Aluminum w/ Stake, Bronze, 7W LED, Narrow Flood – 100 lm/W

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS
Number Of Pieces	1
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	7
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	600
Efficacy	100 lm/W
Product data	
Order product name	BULLYTE,MICRO,W/STAKE
Order code	BL616-HS7LED7NFW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400446475
Net Weight (Piece)	0.010 kg
Catalog Number	BL616-HS7LED7NFW
Catalog Number Description	Accent, Aluminum w/ Stake, Bronze, 7W LED, Narrow Flood