



# i15 Inground

## I15 INGROUND, LED

Inground, 12W LED, 4000K, 120V

The revolutionary i1.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i1.5 reinforces HADCO's position as the leader in landscape lighting.

### Product data

<b>General Information</b>			
Lamp Source Code	LED	Order code	I15NFLC
Lamp Watts	17	Local order code	.
Number of Lamps	1	Numerator - Quantity Per Pack	1
Color Temperature	4000K	Numerator - Packs per outer box	1
CRI	80	Material Nr. (12NC)	912400449011
Mounting	In Ground	Net Weight (Piece)	0.010 kg
<b>Operating and Electrical</b>		Commercial Code	I15NFLC
Voltages	120 V	Catalog Number Description	Inground, 12W LED, 4000K, 120V
Luminaire Input Watts	17	Quick Ship	-
<b>Product Data</b>			
Order product name	I15 INGROUND, LED		