



i15 Inground

I15 INGROUND, LED

Inground, 12W LED, Spot Optics, 4000K, 120V

The revolutionary i1.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i1.5 reinforces HADCO's position as the leader in landscape lighting.

Product data

General Information		Order code	I15NSPC
Lamp Source Code	LED	Local order code	.
Lamp Watts	17	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Color Temperature	4000K	Material Nr. (12NC)	912400451082
CRI	80	Net Weight (Piece)	0.010 kg
Mounting	In Ground	Commercial Code	I15NSPC
Operating and Electrical		Catalog Number Description	Inground, 12W LED, Spot Optics, 4000K, 120V
Voltages	120 V	Quick Ship	-
Luminaire Input Watts	17		
Product Data			
Order product name	I15 INGROUND, LED		