



# 5" Lytecaster Reflector Trim

## 5" Basic Baffle Black

### 5" Basic Baffle Black

Step Baffle Wall Washer provides a high intensity, smooth wash of light up to the ceiling line. Dual reflector optics assure effective output with economical light sources while the aluminum step baffle reduces glare.

#### Product data

General Information	
Lamp Envelope Code	ER-30
Lamp Watts	85
Number of Lamps	1
Downlight Type	Open Downlight
Photometric Distribution Type	Direct
Mounting	Recessed
Mechanical and Housing	
Aperture Size Code	5 in
Shape	Round

Product Data	
Order product name	BASIC WHITE BAFFLE REFLECTOR TRIM
EAN/UPC - Product	784197107604
Order code	1076WH
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400461847
Net Weight (Piece)	0.001 kg
Catalog Number	1076WH
Catalog Number Description	5" Basic Baffle Black