



Roughlyte Vaportight

VWXL10A

INC, 75W, 120V, Wall Mount, Roughlyte, Lexan Globe

The Roughlyte Compact Fluorescent Series is available in 26, 32 and 42 watt lamps. Applications include restaurants, taverns or nightclubs, food courts, atriums or plazas, malls, retail outlets, stores, athletic clubs and facilities, theatres, arenas, stadiums and amusement parks. Heat and shock resistant, prismatic glass optical chamber with neoprene gasketing. Low-glare clear prismatic glass globe standard. Approximately 40% uplight. UL 1598 listed for wet locations – Globe down only. Not recommended for hazardous locations.;

The Roughlyte Incandescent Series is available in wattages ranging from 75 to 200. Applications include wall, columns, ceilings and canopys in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

Product data

General Information		EAN/UPC - Product	190096001330
Lamp Source Code	Incandescent	Order code	VWXL10A
Lamp Watts	75	Local order code	.
Number of Lamps	1	Numerator - Quantity Per Pack	1
Photometric Distribution Type	Type V	Numerator - Packs per outer box	6
Mounting	Surface	Material Nr. (12NC)	912400468248
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	120 V	Commercial Code	VWXL10A
Product Data		Catalog Number Description	INC, 75W, 120V, Wall Mount, Roughlyte, Lexan Globe
Order product name	VWXL10A	Quick Ship	Service Smart (2 Days) USA