



WP Wall Pack Large

WP401PMA-8

PS, 400W, 120-277V, Wall-Pack

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Pulse Start Metal Halide	EAN/UPC - Product	190096001477
Lamp Watts	400	Order code	WP401PMA-8
Number of Lamps	1	Local order code	.
Photometric Distribution Type	Type IV	Numerator - Quantity Per Pack	1
Mounting	Wall	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400475158
Voltages	120/208/240/277 V	Net Weight (Piece)	0.001 kg
Product Data		Commercial Code	WP401PMA-8
Order product name	WP401PMA-8	Catalog Number Description	PS, 400W, 120-277V, Wall-Pack
		Quick Ship	Service Smart (2 Days) USA