



# WP Wall Pack Large

## PS, 400W, 120-277V, Wall-Pack

PS, 400W, 120-277V, Wall-Pack

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

### Product data

| General Information           |                          |
|-------------------------------|--------------------------|
| Lamp Source Code              | Pulse Start Metal Halide |
| Lamp Watts                    | 400                      |
| Number of Lamps               | 1                        |
| Photometric Distribution Type | Type IV                  |
| Mounting                      | Wall                     |
|                               |                          |
| Operating and Electrical      |                          |
| Voltages                      | 120/208/240/277 V        |
|                               |                          |
| Product Data                  |                          |
| Order product name            | WP401PMA-8               |

|                                 |                               |
|---------------------------------|-------------------------------|
| EAN/UPC - Product               | 190096001477                  |
| Order code                      | WP401PMA-8                    |
| Numerator - Quantity Per Pack   | 1                             |
| Numerator - Packs per outer box | 1                             |
| Material Nr. (12NC)             | 912400475158                  |
| Net Weight (Piece)              | 0.001 kg                      |
| Catalog Number                  | WP401PMA-8                    |
| Catalog Number Description      | PS, 400W, 120-277V, Wall-Pack |