



WPM Wall Pack Medium

PS, 70W, 120/277V, Wall-Pack

PS, 70W, 120/277V, Wall-Pack

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

Product data

General Information	
Lamp Source Code	Pulse Start Metal Halide
Lamp Watts	70
Number of Lamps	1
Photometric Distribution Type	Type IV
Mounting	Wall
Operating and Electrical	
Voltages	120/277 V
Product Data	
Order product name	WPM71MAL-6

EAN/UPC - Product	190096005499
Order code	WPM71MAL-6
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400475164
Net Weight (Piece)	0.001 kg
Catalog Number	WPM71MAL-6
Catalog Number Description	PS, 70W, 120/277V, Wall-Pack