



# Roughlyte Vaportight

**INC, 100W, 120V, Ceiling Mount, Roughlyte, Glass Globe/Cast Guard w/ 3/4" Conduit Taps**

INC, 100W, 120V, Ceiling Mount, Roughlyte, Glass Globe/Cast Guard w/ 3/4" Conduit Taps

The Roughlyte Compact Fluorescent Series is available in 26, 32 and 42 watt lamps. Applications include restaurants, taverns or nightclubs, food courts, atriums or plazas, malls, retail outlets, stores, athletic clubs and facilities, theatres, arenas, stadiums and amusement parks. Heat and shock resistant, prismatic glass optical chamber with neoprene gasketing. Low-glare clear prismatic glass globe standard. Approximately 40% uplight. UL 1598 listed for wet locations – Globe down only. Not recommended for hazardous locations. The Roughlyte Incandescent Series is available in wattages ranging from 75 to 200. Applications include wall, columns, ceilings and canopies in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

## Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Photometric Distribution Type	Type V
Mounting	Surface

Operating and Electrical	
Voltages	120 V

Product Data	
Order product name	VCXL11GC WITH 3/4" ROUND BOX
EAN/UPC - Product	190096001354
Order code	VCXL11GC3/4
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

# Roughlyte Vaportight

Material Nr. (12NC)	912400477177
Net Weight (Piece)	0.001 kg
Catalog Number	VCXL11GC3/4
Catalog Number Description	INC, 100W, 120V, Ceiling Mount, Roughlyte, Glass Globe/Cast Guard w/ 3/4" Conduit Taps

