



WP Wall Pack Large

WP251PMAL-8

PS, 250W, 120-277V, w/Lamp, Wall-Pack, Bronze

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

Product data

General Information		EAN/UPC - Product		190096001163
Lamp Source Code	Pulse Start Metal Halide	Order code	WP251PMAL-8	
Lamp Watts	250	Local order code	.	
Number of Lamps	1	Numerator - Quantity Per Pack	1	
Photometric Distribution Type	Type IV	Numerator - Packs per outer box	1	
Mounting	Wall	Material Nr. (12NC)	912400477231	
Operating and Electrical		Net Weight (Piece)	0.001 kg	
Voltages	120/208/240/277 V	Commercial Code	WP251PMAL-8	
Product Data		Catalog Number Description	PS, 250W, 120-277V, w/Lamp, Wall-Pack, Bronze	
Order product name	WP251PMAL-8	Quick Ship	Service Smart (2 Days) USA	