



# WP Wall Pack Large

**PS, 250W, 120-277V, w/Lamp, Wall-Pack, Bronze**

PS, 250W, 120-277V, w/Lamp, Wall-Pack, Bronze

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

## Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>	190096001163
Lamp Source Code	Pulse Start Metal Halide	Order code	WP251PMAL-8
Lamp Watts	250	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	Type IV	Material Nr. (12NC)	912400477231
Mounting	Wall	Net Weight (Piece)	0.001 kg
<b>Operating and Electrical</b>		Catalog Number	WP251PMAL-8
Voltages	120/208/240/277 V	Catalog Number Description	PS, 250W, 120-277V, w/Lamp, Wall-Pack, Bronze
<b>Product Data</b>			
Order product name	WP251PMAL-8		