



WP Wall Pack Large

PS, 400W, 120-277V, w/lamp, Wall-Pack, Bronze

PS, 400W, 120-277V, w/lamp, Wall-Pack, Bronze

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

Product data

General Information	
Lamp Source Code	Pulse Start Metal Halide
Lamp Watts	400
Number of Lamps	1
Photometric Distribution Type	Type IV
Mounting	Wall
Operating and Electrical	
Voltages	120/208/240/277 V
Product Data	
Order product name	WP401PMAL-8

EAN/UPC - Product	190096001187
Order code	WP401PMAL-8
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400477237
Net Weight (Piece)	0.001 kg
Catalog Number	WP401PMAL-8
Catalog Number Description	PS, 400W, 120-277V, w/lamp, Wall-Pack, Bronze