



# WPM Wall Pack Medium

## WPM150LX-8 W/LAMP (SPECIAL)

HPS, 150W, 120-277V, w/Lamp, Wall-Pack

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

### Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>		190096005833
Lamp Source Code	High Pressure Sodium	Order code	WPM150LXL-8	
Lamp Watts	150	Local order code	.	
Number of Lamps	1	Numerator - Quantity Per Pack	1	
Photometric Distribution Type	Type IV	Numerator - Packs per outer box	1	
Mounting	Wall	Material Nr. (12NC)	912400477243	
<b>Operating and Electrical</b>		Net Weight (Piece)	0.001 kg	
Voltages	120/208/240/277 V	Commercial Code	WPM150LXL-8	
<b>Product Data</b>		Catalog Number Description	HPS, 150W, 120-277V, w/Lamp, Wall-Pack	
Order product name	WPM150LX-8 W/LAMP (SPECIAL)	Quick Ship	-	