



# GP Flood Series - GP4

**HPS, 400W, 120-277V, w/Lamp, Trunnion, Flood**

HPS, 400W, 120-277V, w/Lamp, Trunnion, Flood

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

## Product data

General Information		EAN/UPC - Product	
Lamp Source Code	High Pressure Sodium	Order code	GP4T400LXL-8
Lamp Watts	400	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	Flood	Material Nr. (12NC)	912400478448
Mounting	Ground / Floor	Net Weight (Piece)	13607.760 g
Operating and Electrical		Catalog Number	GP4T400LXL-8
Voltages	120/208/240/277 V	Catalog Number Description	HPS, 400W, 120-277V, w/Lamp, Trunnion, Flood
Maximum Lamp Watts	400		
Product Data			
Order product name	GP4T400LXL-8		