



# GP Flood Series - GP2

## GENLYTE FLD,SMALL,ARM,100NLXL1

HPS, 100W, 120V, 2/Lamp, Flood

The GP2 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP2 Flood series is available with ED17 lamps for pulse start metal halide and B17 lamps for high pressure sodium up to 175 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 30 LEDs in either 40W or 60W configurations.

### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	High Pressure Sodium	Order code	GP2A100NLXL-1
Lamp Watts	100	Local order code	.
Number of Lamps	1	Numerator - Quantity Per Pack	1
Photometric Distribution Type	NEMA 7H x 6V	Numerator - Packs per outer box	1
Mounting	Ground / Floor	Material Nr. (12NC)	912400480744
Operating and Electrical		Net Weight (Piece)	0.010 kg
Voltages	120 V	Commercial Code	GP2A100NLXL-1
Maximum Lamp Watts	100	Catalog Number Description	HPS, 100W, 120V, 2/Lamp, Flood
Product Data		Quick Ship	-
Order product name	GENLYTE FLD,SMALL,ARM,100NLXL1		