



# GP Flood Series - GP2

## HPS, 100W, 120V, 2/Lamp, Flood

HPS, 100W, 120V, 2/Lamp, Flood

The GP2 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP2 Flood series is available with ED17 lamps for pulse start metal halide and B17 lamps for high pressure sodium up to 175 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 30 LEDs in either 40W or 60W configurations.

### Product data

General Information	
Lamp Source Code	High Pressure Sodium
Lamp Watts	100
Number of Lamps	1
Photometric Distribution Type	NEMA 7H x 6V
Mounting	Ground / Floor
Operating and Electrical	
Voltages	120 V
Maximum Lamp Watts	100
Product Data	
Order product name	GENLYTE FLD,SMALL,ARM,100NLXL1

EAN/UPC - Product	190096002528
Order code	GP2A100NLXL-1
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400480744
Net Weight (Piece)	0.010 kg
Catalog Number	GP2A100NLXL-1
Catalog Number Description	HPS, 100W, 120V, 2/Lamp, Flood