



GP Flood Series - GP3

PS, 250W, 120-277V, w/Lamp, Trunnion, Flood

PS, 250W, 120-277V, w/Lamp, Trunnion, Flood

The GP3 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP3 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 49 LEDs and a 103W configuration.

Product data

| General Information | | EAN/UPC - Product | |
|-------------------------------|--------------------------|---------------------------------|---------------------------------------------|
| Lamp Source Code | Pulse Start Metal Halide | Order code | GP3T250PMAL-8 |
| Lamp Watts | 250 | Numerator - Quantity Per Pack | 1 |
| Number of Lamps | 1 | Numerator - Packs per outer box | 1 |
| Photometric Distribution Type | NEMA 6H x 6V | Material Nr. (12NC) | 912400480760 |
| Mounting | Ground / Floor | Net Weight (Piece) | 0.001 kg |
| Operating and Electrical | | Catalog Number | GP3T250PMAL-8 |
| Voltages | 120/208/240/277 V | Catalog Number Description | PS, 250W, 120-277V, w/Lamp, Trunnion, Flood |
| Maximum Lamp Watts | 250 | | |
| Product Data | | | |
| Order product name | GP3T250PMAL-8 | | |