



# GP Flood Series - GP5

## HPS, 1000W, 120-277V, w/Lamp, Trunnion, Flood

HPS, 1000W, 120-277V, w/Lamp, Trunnion, Flood

The GP5 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP5 Flood series is available with BT56 lamps for metal halide and E25 lamps for high pressure sodium up to 1500 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP 5 is also available in a 165 W very-long life induction source for 100 000 hours.

### Product data

| General Information           |                      |
|-------------------------------|----------------------|
| Lamp Source Code              | High Pressure Sodium |
| Lamp Watts                    | 1000                 |
| Number of Lamps               | 1                    |
| Photometric Distribution Type | Flood                |
| Mounting                      | Ground / Floor       |

  

| Operating and Electrical |           |
|--------------------------|-----------|
| Voltages                 | 120/277 V |
| Maximum Lamp Watts       | 1000      |

  

| Product Data       |               |
|--------------------|---------------|
| Order product name | GP5T1000LXL-8 |

  

|                                 |   |
|---------------------------------|---|
| EAN/UPC – product               | 190096002771                                  |
| Order code                      | GP5T1000LXL-8                                 |
| Numerator – quantity per pack   | 1   |
| Numerator – packs per outer box | 1   |
| Material no. (12NC)             | 912400480779                                  |
| Net weight (piece)              | 31751.440 g                                   |
| Commercial Code                 | GP5T1000LXL-8                                 |
| Commercial Code                 | HPS, 1000W, 120-277V, w/Lamp, Trunnion, Flood |