



GP Flood Series - GP5

HPS, 1000W, 120-277V, w/Lamp, Trunnion, Flood

HPS, 1000W, 120-277V, w/Lamp, Trunnion, Flood

The GP5 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP5 Flood series is available with BT56 lamps for metal halide and E25 lamps for high pressure sodium up to 1500 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP 5 is also available in a 165W very-long life induction sources for 100,000 hours.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	High Pressure Sodium	Order code	GP5T1000LXL-8
Lamp Watts	1000	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	Flood	Material Nr. (12NC)	912400480779
Mounting	Ground / Floor	Net Weight (Piece)	31751.440 g
Operating and Electrical		Catalog Number	GP5T1000LXL-8
Voltages	120/277 V	Catalog Number Description	HPS, 1000W, 120-277V, w/Lamp, Trunnion, Flood
Maximum Lamp Watts	1000		
Product Data			
Order product name	GP5T1000LXL-8		