



Roughlyte Vaportight

VCXL,26W,HFL,ELEC.BLST,UNV

CFL, 26W, 120V, Ceiling Mount, Roughlyte, Glass Globe/Cast Guard w/Lamp

The Roughlyte Compact Fluorescent Series is available in 26, 32 and 42 watt lamps. Applications include restaurants, taverns or nightclubs, food courts, atriums or plazas, malls, retail outlets, stores, athletic clubs and facilities, theatres, arenas, stadiums and amusement parks. Heat and shock resistant, prismatic glass optical chamber with neoprene gasketing. Low-glare clear prismatic glass globe standard. Approximately 40% uplight. UL 1598 listed for wet locations – Globe down only. Not recommended for hazardous locations. The Roughlyte Incandescent Series is available in wattages ranging from 75 to 200. Applications include wall, columns, ceilings and canopys in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

Product data

General Information	
Lamp Source Code	Compact Fluorescent
Lamp Watts	26
Number of Lamps	1
Photometric Distribution Type	Type V
Mounting	Surface
Operating and Electrical	
Voltages	120 V

Product Data	
Order product name	VCXL,26W,HFL,ELEC.BLST,UNV
EAN/UPC - Product	190096001378
Order code	VCXL26HFLEB-8
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400481846
Net Weight (Piece)	0.001 kg
Commercial Code	VCXL26HFLEB-8

Roughlyte Vaportight

Catalog Number	Description
	CFL, 26W, 120V, Ceiling Mount, Roughlyte, Glass Globe/Cast Guard w/Lamp
Quick Ship	Service Smart (2 Days) USA

