



Twilighter Wall Pack LED

TLW10LED4KPCB-1

LED, 14W, 120V, 4000K, Photocontrol, Wall-Pack - 50 lm/W

Twilighter Series Wallprism is excellent for security, accent and perimeter lighting. Applications include entrance ways, garages, tunnels, overpasses and alleys. It includes a vandal-resistant polycarbonate housing and aluminum reflector for smooth "down-and-out" distribution. Also available with LED sources for a long life of 50,000 hours.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	14
Color Temperature	4000K
Photometric Distribution Type	Type IV
Mounting	Wall

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	14

Initial Performance (IEC Compliant)	
Luminaire Lumens	700
Efficacy	50 lm/W

Product Data	
Order product name	TLW10LED4KPCB-1
EAN/UPC - Product	190096001491
Order code	TLW10LED4KPCB-1
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400486648
Net Weight (Piece)	0.001 kg
Commercial Code	TLW10LED4KPCB-1
Catalog Number Description	LED, 14W, 120V, 4000K, Photocontrol, Wall-Pack
Quick Ship	Service Smart (2 Days) USA