



# LytePro 7 LED Wall Sconce

**LPW7, 14W COB LED, 350mA, 4000K, 120-277V, Dark gray textured paint**

LPW7, 14W COB LED, 350mA, 4000K, 120-277V, Dark gray textured paint – 82 lm/W

The low profile silhouette and compact appearance of LytePro 7 LED wall sconces have high appeal across many building styles. Its low profile styling is ideally suited for use over doorways, garages, entranceways, wall signs or any applications where a lower mounting height and compact size is desired. LytePro 7 consumes only 14 watts, and achieves up to 86 LPW to provide an efficient alternative to traditional light sources.

## Product data

General Information		Approval and Application	
Lamp Source Code	LED	ETL	
Colour Temperature	4000k		
CRI	70	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Type II	Luminaire Lumens	1200
Mounting	Wall	Efficacy	82 lm/W
B.U.G. Rating	B1UOG1	Application Conditions	
Operating and Electrical		+40 °C	
Voltages	120/208/240/277 V	-30 °C	
Luminaire Input Watts	14	Product Data	
		Order product name	LPW7-8DGY

## LytePro 7 LED Wall Sconce

<b>EAN/UPC – product</b>	190096011193
<b>Order code</b>	LPW7-8DGY
<b>Numerator – quantity per pack</b>	1
<b>Numerator – packs per outer box</b>	6
<b>Material no. (12NC)</b>	912400531018
<b>Net weight (piece)</b>	0.001 kg

<b>Commercial Code</b>	LPW7-8DGY
<b>Commercial Code</b>	LPW7, 14W COB LED, 350mA, 4000K, 120-277V, Dark gray textured paint

