



LytePro 7 LED Wall Sconce

COB LED, 14W, 350mA, 4000K, 120V, Textured Bronze w/Button Photocell

COB LED, 14W, 350mA, 4000K, 120V, Textured Bronze w/Button Photocell – 82 lm/W

The low profile silhouette and compact appearance of LytePro 7 LED wall sconces have high appeal across many building styles. Its low profile styling is ideally suited for use over doorways, garages, entranceways, wall signs or any applications where a lower mounting height and compact size is desired. LytePro 7 utilizes only 14 watts, and achieves up to 86 LPW to provide an efficient alternative to traditional light sources.

Product data

General Information		Approval and Application	
Lamp Source Code	LED	Safety Listing	ETL
Colour Temperature	4000K	Initial Performance (IEC Compliant)	
CRI	70	Luminaire Lumens	1200
Photometric Distribution Type	Type II	Efficacy	82 lm/W
Mounting	Wall	Application Conditions	
B.U.G. Rating	B1U0G1	Max Ambient Temp	+40 °C
Operating and Electrical		Min Ambient Temp	-30 °C
Voltages	120 V	Product Data	
Luminaire Input Watts	14	Order product name	LPW7-1BZPCB

LytePro 7 LED Wall Sconce

EAN/UPC - Product	190096011179
Order code	LPW7-1BZPCB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400531021
Net Weight (Piece)	0.001 kg

Catalog Number	LPW7-1BZPCB
Catalog Number Description	COB LED, 14W, 350mA, 4000K, 120V, Textured Bronze w/Button Photocell

