



LytePro 16 LED Wall Sconce

LPW16-78BZ

LPW16, 40W, 700mA, 4000K, 120-277V, Bronze textured paint - 93 lm/W

The architecturally styled LytePro 16 LED Wall Sconce is a compact LED luminaire designed for exterior wall mounting in commercial and residential applications. It is ideal for general-purpose illumination along perimeters, entrances and garages for safety and security installations as well as accent lighting around buildings. LytePro 16 utilizes only 40 watts, and achieves up to 96 LPW to provide an efficient alternative to traditional light sources.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000k
CRI	70
Photometric Distribution Type	Type III
Mounting	Wall
B.U.G. Rating	B1U0G1
Awards	DLC QPL
Operating and Electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	36
Approval and Application	
Safety Listing	ETL

DesignLights Consortium Qualified Product List	
Initial Performance (IEC Compliant)	
Luminaire Lumens	3400
Efficacy	93 lm/W
Application Conditions	
Max Ambient Temp	+40 °C
Min Ambient Temp	-40 °C
Product Data	
Order product name	LPW16-78BZ
EAN/UPC - Product	190096011247
Order code	912400531024
Local order code	.

LytePro 16 LED Wall Sconce

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400531024
Net Weight (Piece)	0.001 kg
Commercial Code	LPW16-78BZ

Catalog Number Description	LPW16, 40W, 700mA, 4000K, 120-277V, Bronze textured paint
Quick Ship	Service Smart (2 Days) Canada

