



LytePro 16 LED Wall Sconce

LED, 30W, 530mA, 4000K, 120-277V, Textured Bronze

LED, 30W, 530mA, 4000K, 120-277V, Textured Bronze – 96 lm/W

The architecturally styled LytePro 16 LED Wall Sconce is a compact LED luminaire designed for exterior wall mounting in commercial and residential applications. It is ideal for general-purpose illumination along perimeters, entrances and garages for safety and security installations as well as accent lighting around buildings. LytePro 16 utilizes only 40 watts, and achieves up to 96 LPW to provide an efficient alternative to traditional light sources.

Product data

| General Information | | Approval and Application | |
|-------------------------------|-------------------|--|--|
| Lamp Source Code | LED | Safety Listing | ETL |
| Colour Temperature | 4000K | DesignLights Consortium Qualified Product List | DesignLights Consortium Qualified Product List |
| CRI | 70 | Initial Performance (IEC Compliant) | |
| Photometric Distribution Type | Type III | Luminaire Lumens | 2700 |
| Mounting | Wall | Efficacy | 96 lm/W |
| B.U.G. Rating | B1U0G1 | Application Conditions | |
| Awards | DLC QPL | Max Ambient Temp | +40 °C |
| Operating and Electrical | | Min Ambient Temp | -40 °C |
| Voltages | 120/208/240/277 V | | |
| Luminaire Input Watts | 28 | | |

LytePro 16 LED Wall Sconce

Product Data

| | |
|---------------------------------|--------------|
| Order product name | LPW16-58BZ |
| EAN/UPC - Product | 190096011223 |
| Order code | LPW16-58BZ |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 912400531032 |

| | |
|----------------------------|--|
| Net Weight (Piece) | 0.001 kg |
| Catalog Number | LPW16-58BZ |
| Catalog Number Description | LED, 30W, 530mA, 4000K, 120-277V, Textured Bronze |

