



# LytePro 16 LED Wall Sconce

LED, 30W, 530mA, 4000K, 120V, Textured Bronze w/Button Photocell

LED, 30W, 530mA, 4000K, 120V, Textured Bronze w/Button Photocell – 96 lm/W

The architecturally styled LytePro 16 LED Wall Sconce is a compact LED luminaire designed for exterior wall mounting in commercial and residential applications. It is ideal for general-purpose illumination along perimeters, entrances and garages for safety and security installations as well as accent lighting around buildings. LytePro 16 utilizes only 40 watts, and achieves up to 96 LPW to provide an efficient alternative to traditional light sources.

## Product data

General Information		Approval and Application	
Lamp Source Code	LED	Safety Listing	ETL
Colour Temperature	4000K	DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List
CRI	70	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Type III	Luminaire Lumens	2700
Mounting	Wall	Efficacy	96 lm/W
B.U.G. Rating	B1U0G1	Application Conditions	
Awards	DLC QPL	Max Ambient Temp	+40 °C
Operating and Electrical		Min Ambient Temp	-40 °C
Voltages	120 V		
Luminaire Input Watts	28		

## LytePro 16 LED Wall Sconce

### Product Data

Order product name	LPW16-51BZPCB
EAN/UPC - Product	190096011216
Order code	LPW16-51BZPCB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400531033

Net Weight (Piece)	0.001 kg
Catalog Number	LPW16-51BZPCB
Catalog Number Description	LED, 30W, 530mA, 4000K, 120V, Textured Bronze w/Button Photocell

