



# SlimSurface LED Downlight

## SLIM 10" R 90CRI 30K ELV/TRIAC BK

### SLIM 10" R 90CRI 30K ELV/Triac BK

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

#### Product data

| General Information    |                                   | EAN/UPC - Product               |                                   |
|------------------------|-----------------------------------|---------------------------------|-----------------------------------|
| Lamp Source Code       | LED                               | Order code                      | S10R930K22BK                      |
| Color Temperature      | 3000K                             | Local order code                | .                                 |
| CRI                    | 90                                | Numerator - Quantity Per Pack   | 1                                 |
| Downlight Type         | Lensed Downlight                  | Numerator - Packs per outer box | 1                                 |
| Mounting               | Surface                           | Material Nr. (12NC)             | 912400542304                      |
| Mechanical and Housing |                                   | Net Weight (Piece)              | 0.200 kg                          |
| Aperture Size Code     | 10 in                             | Commercial Code                 | S10R930K22BK                      |
| Product Data           |                                   | Catalog Number Description      | SLIM 10" R 90CRI 30K ELV/Triac BK |
| Order product name     | SLIM 10" R 90CRI 30K ELV/TRIAC BK |                                 |                                   |