



# SlimSurface LED Downlight

## SLIM 10" R 80CRI 30K ELV/Triac MT

### SLIM 10" R 80CRI 30K ELV/Triac MT

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

#### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	LED	Order code	S10R830K22MT
Colour Temperature	3000K	Numerator - Quantity Per Pack	1
CRI	80	Numerator - Packs per outer box	1
Downlight Type	Lensed Downlight	Material Nr. (12NC)	912400542322
Mounting	Surface	Net Weight (Piece)	0.200 kg
Mechanical and Housing		Catalog Number	S10R830K22MT
Aperture Size Code	10 in	Catalog Number Description	SLIM 10" R 80CRI 30K ELV/Triac MT
Product Data			
Order product name	SLIM 10" R 80CRI 30K ELV/TRIAC MT		