



# Mini Gimbal Downlight LED

## Mini Gimbal 3" 90 CRI 30K Black NF

Mini Gimbal 3" 90 CRI 30K Black NF - 74 lm/W

The Lightolier LED Mini Gimbal downlight lets you emphasize without the size. The product is easily adjustable below ceiling to highlight the object or surface. The small detachable junction box eliminates the need for a traditional frame or bulky remodeler kit, making installation quick and easy.

### Product data

General information	
Lamp Source Code	LED
Colour Temperature	3000 K
CRI	90
Downlight Type	Accent Downlight
Photometric Distribution Type	Medium
Mounting	Recessed T-Bar / T-Grid
Fixture Finish	Black
Number Of Pieces	1
Grade	Value Grade

### Operating and electrical

Voltages	120 V
Luminaire Input Watts	8
Conduit Connection	7/8 inch knockout

### Mechanical and housing

Aperture Size Code	3 in
--------------------	------

Enclosure	Metal and Plastic
-----------	-------------------

### Approval and application

Energy Certifications	cETLus Energy Star Title 24 JA8
-----------------------	---------------------------------

### Initial performance (IEC compliant)

Luminaire Lumens	550
Efficacy	74 lm/W

### Product data

Order product name	Mini Gimbal 3" 90 CRI 30K Black NF
EAN/UPC - Product	190096017287
Order code	MG3R06930NF1B
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material Nr. (12NC)	912400543521
Net Weight (Piece)	0.295 kg
Catalog Number	MG3R06930NF1B

# Mini Gimbal Downlight LED

Catalog Number	Description
	Mini Gimbal 3" 90 CRI 30K Black NF

