



Mini Gimbal Downlight LED

Mini Gimbal 3" 90 CRI 30K Brushed Nickel NF

Mini Gimbal 3" 90 CRI 30K Brushed Nickel NF - 74 lm/W

The Lightolier LED Mini Gimbal downlight lets you emphasize without the size. The product is easily adjustable below ceiling to highlight the object or surface. The small detachable junction box eliminates the need for a traditional frame or bulky remodeler kit, making installation quick and easy.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	3000 K
CRI	90
Downlight Type	Accent Downlight
Photometric Distribution Type	Medium
Mounting	Recessed T-Bar / T-Grid
Fixture Finish	Brushed Nickel
Number Of Pieces	1
Grade	Value Grade

Operating and electrical	
Voltages	120 V
Luminaire Input Watts	8
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Aperture Size Code	3 in

Enclosure	Metal and Plastic
-----------	-------------------

Approval and application	
Energy Certifications	cETLus Energy Star Title 24 JA8

Initial performance (IEC compliant)	
Luminaire Lumens	550
Efficacy	74 lm/W

Product data	
Order product name	Mini Gimbal 3" 90 CRI 30K Brush Nick NF
EAN/UPC - Product	190096017294
Order code	MG3R06930NF1N
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material Nr. (12NC)	912400543522
Net Weight (Piece)	0.295 kg
Catalog Number	MG3R06930NF1N

Mini Gimbal Downlight LED

Catalog Number	Description
	Mini Gimbal 3" 90 CRI 30K Brushed Nickel NF

