



Mini Downlight LED

Mini Downlight 90CRI 3000K White F

Mini Downlight 90CRI 3000K White F - 74 lm/W

The small detachable junction box eliminates the need for a traditional frame or bulky remodeler kit, making installation quick and easy.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	3000 K
CRI	90
Downlight Type	Accent Downlight
Photometric Distribution Type	Flood
Mounting	Recessed T-Bar / T-Grid
Fixture Finish	White
Number Of Pieces	1
Grade	Value Grade
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	8
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Aperture Size Code	3 in
Shape	Round
Enclosure	Metal and Plastic

Approval and application	
Energy Certifications	cETLus Energy Star Title 24 JA8
Initial performance (IEC compliant)	
Luminaire Lumens	550
Efficacy	74 lm/W
Product data	
Order product name	Mini Downlight 90CRI 3000K White F
EAN/UPC - Product	190096017409
Order code	MD3R069301FW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material Nr. (12NC)	912400543533
Net Weight (Piece)	0.300 kg
Catalog Number	MD3R069301FW
Catalog Number Description	Mini Downlight 90CRI 3000K White F