



DuaLED Recessed

2x2, 2700 Nominal Delivered Lumens, 4000K, Diffuse

2x2, 2700 Nominal Delivered Lumens, 4000K, Diffuse - 96 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

| General Information | | Mechanical and Housing | |
|-------------------------------|---------------|-------------------------------------|------------------------|
| Lamp Source Code | LED | Fixture Size | 2 ft x 2 ft |
| Colour Temperature | 4000K | Shape | Square |
| CRI | 80 | Initial Performance (IEC Compliant) | |
| Photometric Distribution Type | Direct | Luminaire Lumens | 2700 |
| Mounting | Recessed | Efficacy | 96 lm/W |
| Operating and Electrical | | Product Data | |
| Voltages | 120/277/347 V | Order product name | 2DLG27L840-2-D-UNV |
| Luminaire Input Watts | 28 | EAN/UPC - Product | 781370181307 |
| | | Order code | 2DLG27L840-2-D-UNV-DIM |

DuaLED Recessed

| | |
|---------------------------------|--------------|
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401044236 |
| Net Weight (Piece) | 0.001 kg |

| | |
|----------------------------|--|
| Catalog Number | 2DLG27L840--2-D-UNV-DIM |
| Catalog Number Description | 2x2, 2700 Nominal Delivered Lumens, 4000K, Diffuse |

