



60 Series Exits

60MLA1GW

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Green Letters, White Housing and White Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information		Local order code	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912401045913
Voltages	120/277 V	Net Weight (Piece)	0.100 kg
Luminaire Input Watts	4	Commercial Code	60MLA1GW
Product Data		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Green Letters, White Housing and White Stencil
Order product name	60MLA1GW	Quick Ship	-
EAN/UPC - Product	781370995355		
Order code	912401045913		