



# 60 Series Exits

## 60MLA1GBA

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Green Letters, Black Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

General Information	
Lamp Source Code	LED
Mounting	Wall Suspended
Operating and Electrical	
Voltages	120/277 V
Luminaire Input Watts	4
Product Data	
Order product name	60MLA1GBA
EAN/UPC - Product	781370995393
Order code	912401045916

Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401045916
Net Weight (Piece)	0.100 kg
Commercial Code	60MLA1GBA
Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Green Letters, Black Housing and Brushed Aluminum Stencil
Quick Ship	-