



# FlexScape Accent BL9

Accent, LED Architectural Accent, FlexScape, Bronze, 3000K, 12V

Accent, LED Architectural Accent, FlexScape, Bronze, 3000K, 12V

The Hadco FlexScape LED accent luminaire BL9 brings landscape lighting to the next level. Designed for optimal LED performance, it provides the lighting professional with countless low-voltage options. The luminaire's rugged die-cast aluminium housing features low-energy outdoor lighting. Convenient beam adjustability makes for easy on-site lighting effect changes. The lockable aiming is well-suited for accenting objects, textures, walls and trees, etc. This all-weather luminaire comes with 100% moulded silicone gaskets.

## Product data

| General information           |                   |
|-------------------------------|-------------------|
| Lamp source code              | LED               |
| Lamp wattage                  | 11                |
| Number of lamps               | 1                 |
|                               | 3000 K            |
| CRI                           | 70                |
| Photometric distribution type | General Diffuse   |
| Mounting                      | NPT/NPS           |
| Number Of Pieces              | 1                 |
| Operating and electrical      |                   |
| Voltages                      | 12 V              |
| Luminaire input watts         | 11                |
| Conduit Connection            | 7/8 inch knockout |

| Mechanical and housing              |                            |
|-------------------------------------|----------------------------|
| Enclosure                           | Metal and Plastic          |
| Initial performance (IEC compliant) |                            |
| Luminaire lumens                    | 700                        |
| Product data                        |                            |
| Order product name                  | FLEXSCAPE,ACCENT,WW,BRONZE |
| EAN/UPC – product                   | 783352020819               |
| Order code                          | BL9DW-HS7                  |
| SAP numerator – quantity per pack   | 1                          |
| Numerator – packs per outer box     | 1                          |
| SAP material                        | 912401150002               |
| Net Weight (Piece)                  | 0.001 kg                   |

# FlexScape Accent BL9

|                              |  |
|------------------------------|--|
| Commercial Code              | BL9DW-HS7  |
| Catalogue number description | Accent, LED Architectural Accent, FlexScape, Bronze,<br>3000K, 12V |

