



# FlexScape Accent BL9

Accent, LED Architectural Accent, FlexScape, Bronze, 4000K, 12V

Accent, LED Architectural Accent, FlexScape, Bronze, 4000K, 12V - 100 lm/W

Hadco FlexScape LED accent luminaire BL9 brings landscape lighting to the next level. Designed for optimal LED performance, it provides the lighting professional with countless low-voltage options. The luminaire's rugged die-cast aluminum housing features low-energy outdoor lighting. Convenient beam adjustability makes for easy on-site lighting effect changes. The lockable aiming is well-suited for accenting objects, textures, walls, trees, etc. This all-weather luminaire comes with 100% molded silicone gaskets.

## Product data

General information	
Lamp Source Code	LED
Lamp Watts	11
Number of Lamps	1
Colour Temperature	4000 K
CRI	70
Photometric Distribution Type	General Diffuse
Mounting	NPT/NPS
Number Of Pieces	1

Operating and electrical	
Voltages	12 V
Luminaire Input Watts	11
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	700
Efficacy	100 lm/W

Product data	
Order product name	FLEXSCAPE,ACCENT,CW,BRONZE
EAN/UPC - Product	783352020833
Order code	BL9DC-HS7
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	28
Material Nr. (12NC)	912401150004
Net Weight (Piece)	0.740 kg

FlexScape Accent BL9

Catalog Number	BL9DC-HS7
Catalog Number Description	Accent, LED Architectural Accent, FlexScape, Bronze, 4000K, 12V

